



INSTRUCTIONS FOR

ROLLCABS 4-10 DRAWER

MODEL NO'S: **AP2405, AP2406, AP2407, AP2408, AP2410**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instruction manual

1. SAFETY

- WARNING!** Ensure Health & Safety, local authority, and general workshop practice regulations are adhered to when using this product.
- × **DO NOT** open more than one drawer at a time.
- × **DO NOT** step on the drawers.
- × **DO NOT** let children play with the roll cab.
- ✓ Ensure all drawers are fully closed and the self locking catches are activated, before moving the toolbox.
- ✓ Secure the brakes when rollcab is in the desired position.
- ✓ Keep the work area clean, uncluttered and ensure there is adequate lighting.
- × **DO NOT** use in damp work areas.
- WARNING!** The warnings, cautions and instructions referred to in this instruction manual cannot cover all possible conditions and situations that may occur. It must be understood that common sense and caution are factors which cannot be built into this product, but must be applied by the operator.

2. INTRODUCTION

Heavy gauge steel with double wall construction for extra strength and durability. Ball bearing drawer runners provide superior performance and carry heavier loads. Each drawer fitted with catch to prevent accidental opening when being transported around the workshop. Added security provided by side mounted cylinder lock, supplied with two keys. Rubber grip side handles for comfort and ease when manoeuvring. Rust and solvent resistant powder coat paint finish. Fitted with anti-shock protection on all four corners to prevent accidental damage. Features two Ø125mm swivel castors with large toe locks and two fixed wheels. Tough composite top for fitting and securing top box or can be used as a workstation. Unique design fitted with perforated side panels for hanging tools and accessories.

3. SPECIFICATION

Model No	AP2405	AP2406	AP2407	AP2408	AP2410
Overall Size					
Width	765mm				
Depth	470mm				
Height	960mm				
Drawers (Qty)					
Medium	3	3	5	6	10
Large	1	2	1	2	
X - Large		1	1		
Drawer Width	535mm	535mm	535mm	535mm	535mm
Drawer Depth	390mm	390mm	390mm	390mm	390mm
Drawer Height (Medium)	60mm	60mm	60mm	60mm	60mm
Drawer Height (Large)	130mm	130mm	130mm	130mm	
Drawer Height (X - Large)		195mm	195mm		



AP2405



AP2407



AP2410



AP2406



AP2408

Parts support is available for this product. To obtain a parts listing and/or diagram, please log on to www.sealey.co.uk, email sales@sealey.co.uk or telephone 01284 757500.



Environmental Protection

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain off any fluids (if applicable) into approved containers and dispose of the product and the fluids according to local regulations.

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of this product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.



Sole UK Distributor, Sealey Group.
Kempson Way, Suffolk Business Park,
Bury St. Edmunds, Suffolk.
IP32 7AR



01284 757500



01284 703534



www.sealey.co.uk



sales@sealey.co.uk