



INSTRUCTIONS FOR:

MOBILE WORKBENCH DUCTS MODELS: AP2416 & AP2418

Thank you for purchasing a Sealey product. Manufactured to a high standard this product will, if used according to these instructions and properly maintained, give you years of trouble free performance.



IMPORTANT: READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS AND CAUTIONS. USE THIS PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. RETAIN THESE INSTRUCTIONS FOR FUTURE USE.

1. SAFETY PRECAUTIONS

1.1. GENERAL SAFETY INSTRUCTIONS.

- ✓ Read the operator's manual carefully before using your workbench.
- **X DO NOT** open more than one drawer at a time.
- X DO NOT step on the drawers.
- X DO NOT let children near the workbench.
- ✓ Ensure drawers are fully closed and self locking catch is activated before moving the workbench.
- ✓ Secure brakes when rollcab is in the desired position.

2. INTRODUCTION AND SPECIFICATIONS

Heavy gauge steel with double wall construction for extra strength and durability. Fitted with oversized, heavy-duty Ø160mm castors, two fixed and two locking swivels. Ball bearing drawer runners provide superior performance and carry heavier loads. Each drawer fitted with catch to prevent unexpected opening when being transported around the workshop. Added security provided by side mounted cylinder lock. Two lockable cupboards with internal shelving for added storage. Supplied with six keys, two for drawers, four for cupboards. Rust and solvent resistant powder coat paint finish. Fitted with anti-shock protection on all four corners to prevent accidental damage. Heavy-duty metal work top makes these units very durable and a great workstation. Unique design fitted with perforated side panels for hanging tools and accessories.





	AP2416	AP2418		
Overall Size				
Width	1130mm			
Depth	565mm			
Height	1000mm			
Drawers (Qty)				
Medium	3	6		
Large	2	2		
X - Large	1			
Drawer Width	533mm	533mm		
Drawer Depth	391mm	391mm		
Drawer Height (Medium)	58mm	58mm		
Drawer Height (Large)	128mm	128mm		
Drawer Height (X - Large)	195mm			



Optional Accessories		
Model No	Description	
AP24ACC2	Side Shelf with Paper Roll Holder	
AP24ACC3	Document Holder	
AP24ACC4	Waste Bin	
AP24ACC5	Can and Bottle Holder	
AP24ACC6	Drawer Divider 3 x 395 x 58mm	
AP24ACC7	Drawer Divider 3 x 395 x 120mm	
AP24ACC9	Short Hook Set x 10pcs	
AP24ACC10	Medium Hook Set x 10pcs	


3. OPERATION

Each drawer is fitted with a catch mechanism on the right hand side of the drawer underneath the handle, to open drawer push the catch to the left to release the catch and pull the drawer open (fig.1).

WARNING! Only open one drawer at a time (fig.2) and DO NOT overload the drawers (fig.3) shows the maximum weight per drawer.

When moving the workbench, ensure that the drawers are closed and locked (fig.4) to prevent accidental opening, release the brakes as shown in fig.5 and move the workbench using the handles and maintain full control. When the workbench has been moved to the required location, lock the brakes.

WARNING! DO NOT move across slopes of more than 5 degrees as the workbench may tilt (fig.6).



4. PARTS

Part No	Description	Part No	Description
AP2418.06	Drawer (Medium)	AP2418.11	Wheel Set
AP2418.07	Drawer (Large)	AP2418.12	Anti Shock Protection (Pair)
AP2418.08	Drawer (X-Large)	AP2418.13	Drawer Handle
AP2418.09	Ball Bearing Slide 35mm (Pair)	AP2418.14	Key
AP2418.10	Ball Bearing Slide 27mm (Pair)	AP2418.15	Drawer Handle Lock

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice. **IMPORTANT:** No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

INFORMATION: For a copy of our latest catalogue and promotions call us on 01284 757525 and leave your full name and address, including postcode.







