

# 3W SMD LED FLEXI RECHARGEABLE MAGNETIC PICK-UP TOOL LIGHT

MODEL NO: LEDFLEXPT

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to instructions

# 1. SAFETY

#### 1.1. GENERAL SAFETY

- ✓ Ensure the lamp is fully charged before initial use.
- **DO NOT** turn the lamp on when it is being charged.
- **DO NOT** shine directly into your, another person's or an animal's eyes.
- **DO NOT** allow children to use the lamp.
- **DO NOT** handle or move the lamp whilst it is being charged.
- DO NOT use the lamp if you suspect that the battery or the lamp casing is damaged.
- **DO NOT** leave battery in a discharged state, recharge battery immediately. Before storage, fully recharge the battery, subsequently recharge the battery at least once every six months of non-use.

#### 1.2. BATTERY SAFETY

- □ **WARNING!** To reduce the risk of burns or fire:
- **DO NOT** attempt to open, disassemble, modify or service the battery pack.
- **DO NOT** crush, puncture, short external contacts or dispose of in fire or water.
- DO NOT expose to temperatures above 60°C (140°F).
- ✓ Recycle or dispose of used battery as stipulated by local regulation.
- If the electrolyte in the cells gets on your skin, thoroughly wash with soap and water. If it gets in your eyes, rinse thoroughly with cool water and seek immediate medical attention.

# 2. INTRODUCTION


High power 3W SMD LED produces up to 280 lumens in tight spaces like engine compartments. Features a 300mm heavy-duty flexible neck with the ability to hold its position wherever you need it. Magnetic ring around light for use as a pick-up tool. Features a magnetic base with an adjustable hook for storage. On/off switch controls two lighting options. Supplied with USB Type-C Cable. Over charge and over discharge protection.

# 3. SPECIFICATION

Model No:	LEDFLEXPT
	3.7V 2200mAh Lithium-ion
0 0	3-4hrs
LED Type:	3W SMD
Length:	530mm
Lumen Output:	280lm
Operating Time:	3-20hrs

## 4. OPERATION

- 4.1. Connect the USB lead to the port on the bottom of the torch.
- 4.2. The red LED on the front face of the unit will light whilst the torch is charging.
- 4.3. When the unit is fully charged the green LED on the torch front face will light.
- 4.4. Two different operational modes are available. By depressing the torch on/off switch once a low level white light will be seen
- 4.5. Push a second time and higher level white light will occur.
- 4.6. A third will turn the torch off.
- 4.7. There is a storage hook within the handle for storage purposes.



### 5. MAINTENANCE

- 5.1. Keep the torch clean by wiping with a damp cloth.
- 5.2. Keep battery fully charged if left over long periods of time.
- 5.3. Store torch and batteries in a dry childproof area.
- 5.4. Lamp assembly can be disassembled to clean lens. Simply unscrew cap and wipe clean the lens.



# **ENVIRONMENT PROTECTION**

Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.





## **WEEE REGULATIONS**

Dispose of this product at the end of its working life in compliance with the EU Directive on Waste Electrical and Electronic Equipment (WEEE). When the product is no longer required, it must be disposed of in an environmentally protective way. Contact your local solid waste authority for recycling information.

**Note**: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.